



The refrigerated merchandiser designed for performance and built to last



1-800-247-8709 • www.uselectit.com



## **20% Greater Capacity** When compared with competitors

**Product Flexibility** 

Configurable to almost any package size

**Healthy Safety** 

Programmable by selections, range and row

## **ICART**

7" Touch Screen Optional Customers fill up their shopping cart and can see product nutrition information

Heated Glass Optional Eliminate condensation and fogging









Refrigerant

SNA

Versatility PayRange Onboard



Refresh

Dynamic Advertising Potential Still images and << video clips >> Optional

> Standard Backlit Braille **Keypad**







Evoke VT5 shown with standard 3.5" Display, Braille Identified Keypad and Leg Covers

Evoke 5 Refrigerated Merchandiser						
Selections	Up to 60 Items					
Capacity	Varies with Tray Configuration					
Payment Systems	All Industry standard MDB Compatible Devices					
Data Communication	DEX/UCS					
Refrigeration	Super 1/3 HP, R134A or R-513A (SNAP Compliant)					
Electrical Requirements	Domestic: 115 VAC/60Hz, 5.5 AMPS International: 230 VAC/50Hz, 3 AMPS; With Heated Glass Option: 115 VAC/60Hz, 6.5 AMPS International: 230 VAC/50Hz, 3.5 AMPS					
Dimensions	Height	72" (183cm)	Width	41" (104 cm)	Depth	38" (97cm)
Ship Weight	*811 lbs. (367.8 kg) *Varies with tray configuration and options.					
Standard Features	FLEX Controller with 3.5" LCD Color Display, LED Lighting, iVend® Sensor System, Door Switch, ADA Delivery Bin, Leg Covers, Braille Keypad, Full Health Safety Feature, PayRange Mobile Payment System & ADA Compliant					
Options	7" iCart Touch Screen Interface, Motor Pairing, High Capacity Can Tray, Audio Interface, Custom Coil and Tray Configurations, Custom Colors, Custom Graphics, Kick Panel, Automatic Controller (Heated Glass) & Changeable LED Backlit POS					

In order to bring you the best products possible, we continue to improve product design and performance and as such specifications are subject to change In other to only good the deep produces possion, we contrain the might be produce oblight and perturbative and as back spectrationation as a source spectra of the produce oblight and perturbative and as back spectra of the might be presented on the might be presented on the spectra of the equipment in any application for which it is capable of being used beyond approvals listed on the product. Any purchase is required to make an independent margis of the fitness and legal by the product suggest and before it is depined and must contrain the normality charm required to make an independent margis of the fitness and legal by of the product. Suggest and the product suggest

